



## HF dispersion horn 110° - 60° for P10



### Contents:



Weight: 0.1 kg / 0.2 lb




nexo-sa.com  
ZA du Pre de la Dame Jeanne  
60128 PLAILLY - France

- Read this document before using.
- Keep this document.
- Observe all warnings and cautions.



## Dimensions:



## Use:

<b>1</b> Unlock the 2 quarter-turn screws, Remove the grille.	<b>2</b> Remove the flange to place the PNT-P10FLG11060.
<b>3</b> If necessary, rotate it.	<b>4</b> Magnets keep the horn in place.

- NEXO cannot accept responsibility for accidents caused by any factor other than defects in this product itself.
- Please check the web site [nexo-sa.com](http://nexo-sa.com) for the latest update.

# NEXO

nexo-sa.com  
ZA du Pre de la Dame Jeanne  
60128 PLAILLY - France

- Read this document before using.
- Keep this document.
- Observe all warnings and cautions.

